

## المواصفات الفنية للوحات انداز الغازات الطبية

- Mains input: 85- 265 Vac, single phase, 50/60 Hz.
- External Fuse Rating: 250 V 3A (T) Ceramic
- BMS Relay contacts: single pole changeover  
1A @ 24 Vdc, 0.5A @ 120 Vac. Resistive load
- Remote Audible Relay contacts: single pole changeover  
1A @ 24 Vdc, 0.5A @ 120 Vac. Resistive load
- Battery Backup : 4 hours minimum on battery
- Internal Fuse Rating : 250 V 1A (T) Ceramic
- The panel contains the following features:
  - All electronics contained in an attractive, white stove enameled, robust metal enclosure
  - Open and Short Circuit indication
  - Volume control, permanent mute button and engineers reset button are all easily accessed
  - Up to 6 gases can be displayed on each panel with 4 conditions available for each gas

### الشروط والإحكام

- ٠١ على الشركة المتقدمة للعطاء الكشف على الموقع لمعرفة كيفية دخول الجهاز وتركيبه داخل الموقع
- ٠٢ على الشركة المحال عليها العطاء اخذ موافقة مبدئية من قبل إدارة مستشفى الامير راشد بن الحسن العسكري قبل القيام بأي عمل .
- ٠٣ على الشركة تقديم كفالة على جميع الأعمال المطلوبة .
- ٠٤ تتحمل الشركة المحال عليها العطاء مسؤولية أي عطل او ضرر قد يحدث للأفراد والممتلكات أثناء سير العمل والخدمات الطبية الملكية / مستشفى الامير راشد بن الحسن لا تتحمل أي مسؤولية لتلك الأعطال والأضرار .

العدد	الم لوحات المطلوبه	القسم
٢	Two gas alarm panel (O <sub>2</sub> -VAC) Including Hi/Low pressure switches	قسم التوليد الاول
١	Three alarm panel (O <sub>2</sub> -VAC - Ma) Including Hi/Low pressure switches	قسم التوليد الثاني
١	Three alarm panel (O <sub>2</sub> -VAC - Ma) Including Hi/Low pressure switches	قسم الخداج القديم
١	Three alarm panel (O <sub>2</sub> -VAC - Ma) Including Hi/Low pressure switches	قسم الاطفال
١	four alarm panel (O <sub>2</sub> -VAC - Ma -N <sub>2</sub> O) Including Hi/Low pressure switches	قسم العمليات القديم
١	Two alarm panel (O <sub>2</sub> -VAC) Including Hi/Low pressure switches	قسم الطوارئ القديم
١	Three alarm panel (O <sub>2</sub> -VAC - Ma) Including Hi/Low pressure switches	قسم الطوارئ القديم